



EXTENSION RODS LIST

Refer to Figure A to determine correct rod length for each individual openings installation and adjustability requirements

Model	Description	
EHRO2	1/2" Extension Rod	23.00
EHR1	1" Extension Rod	23.00
EHR15	1-1/2" Extension Rod	27.00
EHR2	2" Extension Rod	34.00
EHR3	3" Extension Rod	34.00
EHR4	4" Extension Rod	45.00
EHR5	5" Extension Rod	56.00

ADJUSTABLE EXTENTION ROD LIST

Model	Description	
EHRA15	1-1/2" Adjustable Extension Rod	27.00
EHRA4	4" Adjustable Extension Rod	45.00

SPECIFY FINISH

Finish	Description	
A	Chrome Powder Coat	N/C
B	Black Powder Coat	20.00

OPTIONS & ACCESSORIES LIST

Model	Description	
EHBB	Surface Back Box 2-25/32" x 4-7/8" x 1-1/2" (71mm x 124mm x 38mm) Supplied with EH30, EH40, EH42	45.00
EHCP	Catch Disk Only Replacement for the catch plate assembly	34.00
EHSBA	Catch Plate Assembly	56.00
EHW	Extension Wrenches Used to tighten extension rods to catch plate assembly	8.00

SPECIFY FINISH FOR SURFACE BACK BOX EHBB

Finish	Description	
A	Chrome Powder Coat	N/C
B	Black Powder Coat	20.00

How To Determine Extension Rod & Adjustable Rod Length

- Extensions Rod Application:** Refer to Fig. A for Aligned Catch Plate and Door Holder
Adjustable Rod Application: Refer to Fig. B for Misaligned Catch Plate and Door Holder
1. Hold door open at desired position.
 2. Measure distance between door and wall.
 3. Subtract below dimension indicated for door holder style

- Flush Mount:** Subtract 3" (76mm) from measured distance to determine minimum rod length.
Recessed Mount: Subtract 2-3/8" (60mm) from measured distance to determine minimum rod length.
Surface Mount: Subtract 4-5/8" (76mm) from measured distance to determine minimum rod length.